

EPOS4 Positioning Controllers Data



motor control

EPOS4 Compact 50/15 EtherCAT

Ready-to-install compact solution, designed for use with brushed DC motors with encoders or brushless EC motors with Hall sensors and encoders up to 750/1500 Watt.

EPOS4 50/5

Positioning controller in a robust housing, designed for use with brushed DC motors with encoders or brushless EC motors with Hall sensors and encoders up to 250/750 Watt.

EPOS4 70/15

Positioning controller in a robust housing, designed for use with brushed DC motors with encoders or brushless EC motors with Hall sensors and encoders up to 1050/2100 Watt.

Controller version		
EtherCAT Slave	CANopen Slave with EtherCAT option	CANopen Slave with EtherCAT option
Electrical data		
10 - 50 VDC	10 - 50 VDC	10 - 70 VDC
10 - 50 VDC	10 - 50 VDC	10 - 70 VDC
0.9 x V _{CC}	0.9 x V _{CC}	0.9 x V _{CC}
30 A (<60 s)	15 A (<15 s)	30 A (<60 s)
15 A	5 A	15 A
50 kHz	50 kHz	50 kHz
25 kHz (40 µs)	25 kHz (40 µs)	25 kHz (40 µs)
2.5 kHz (400 µs)	2.5 kHz (400 µs)	2.5 kHz (400 µs)
2.5 kHz (400 µs)	2.5 kHz (400 µs)	2.5 kHz (400 µs)
50 000 rpm (sinusoidal), 100 000 rpm (block)	50 000 rpm (sinusoidal), 100 000 rpm (block)	50 000 rpm (sinusoidal), 100 000 rpm (block)
2.2 µH / 15 A	15 µH / 5 A	15 µH / 15 A
Inputs		
H1, H2, H3	H1, H2, H3	H1, H2, H3
A, A\, B, B\, I, I\ (max. 6.25 MHz)	A, A\, B, B\, I, I\ (max. 6.25 MHz)	A, A\, B, B\, I, I\ (max. 6.25 MHz)
A, A\, B, B\, I, I\, Clock, Clock\, Data, Data\	A, A\, B, B\, I, I\, Clock, Clock\, Data, Data\	A, A\, B, B\, I, I\, Clock, Clock\, Data, Data\
4 (level switchable: logic/PLC)	4 (level switchable: logic/PLC)	4 (level switchable: logic/PLC)
4, differential	4, differential	4, differential
2 (12-bit resolution, -10...+10 V)	2 (12-bit resolution, -10...+10 V)	2 (12-bit resolution, -10...+10 V)
configurable with DIP switch 1...5	configurable with DIP switch 1...5	configurable with DIP switch 1...5
Outputs		
2	2	2
1, differential	1, differential	1, differential
2 (12-bit resolution, -4...+4 V, max. 1 mA)	2 (12-bit resolution, -4...+4 V, max. 1 mA)	2 (12-bit resolution, -4...+4 V, max. 1 mA)
+5 VDC, max. 70 mA	+5 VDC, max. 70 mA	+5 VDC, max. 70 mA
+5 VDC, max. 30 mA	+5 VDC, max. 30 mA	+5 VDC, max. 30 mA
+5 VDC, max. 145 mA	+5 VDC, max. 145 mA	+5 VDC, max. 145 mA
Interfaces		
-	high; low (max. 1 Mbit/s)	high; low (max. 1 Mbit/s)
100 Mbit/s (Full Duplex)	Optional 581245 EPOS4 EtherCAT Card available	Optional 581245 EPOS4 EtherCAT Card available
-	RxD; TxD (max. 115 200 bit/s)	RxD; TxD (max. 115 200 bit/s)
Data+; Data- (Full Speed)	Data+; Data- (Full Speed)	Data+; Data- (Full Speed)
Indicator		
Green LED, red LED	Green LED, red LED	Green LED, red LED
Environmental conditions		
-30...+25°C	-30...+50°C	-30...+50°C
+25...+77°C; Derating: -0.288 A/°C	+50...+80°C; Derating: -0.167 A/°C	+50...+85°C; Derating: -0.429 A/°C
-40...+85°C	-40...+85°C	-40...+85°C
5...90%	5...90%	5...90%
Mechanical data		
approx. 140 g	approx. 206 g	approx. 372 g
59.5 x 79.5 x 37.8 mm	105.0 x 83.0 x 38.7 mm	125.0 x 94.5 x 38.7 mm
M3 screws	Flange for M4-screws	Flange for M4-screws
Part numbers		
605299 EPOS4 Compact 50/15 EtherCAT	546047 EPOS4 50/5	594385 EPOS4 70/15
Accessories		
235811 DSR 70/30 Shunt regulator	309687 DSR 50/5 Shunt regulator	235811 DSR 70/30 Shunt regulator
Order accessories separately, see page 578	Order accessories separately, see page 578	Order accessories separately, see page 578